



## imVision Controller X (Argentina Only)

### Product Classification

<b>Regional Availability</b>	Latin America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Controller unit
<b>Product Brand</b>	iPatch®

### General Specifications

<b>Color</b>	Cool gray
--------------	-----------

### Dimensions

<b>Height</b>	81.28 mm   3.2 in
<b>Width</b>	19 mm   0.748 in

### Electrical Specifications

<b>Input Voltage</b>	100–240 Vac
<b>Output Current at Voltage, continuous</b>	2.08 A @ 12 Vdc
<b>Power Frequency</b>	50–60 Hz

### Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate   Steel
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	CE   RCM   UL

# 760237877 | imV-CNTRL-X-AR

---

## Packaging and Weights

<b>Included</b>	16 in panel bus jumper   7 ft patch cord   Forty-four position bus panel
<b>Packaging quantity</b>	1
<b>Weight, net</b>	1.288 kg   2.84 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

