



Carrier Access Point with 4-Band Support for Low Power USA 700, USA 750, SMR 800, CEL 850, AWS 1700, and PCS 1900 Applications, Copper Fed, Power over CAT Powered, without Fan Kit

## Product Classification

<b>Product Type</b>	Access point
<b>Product Brand</b>	ERA®
<b>Product Series</b>	CAP L

## General Specifications

<b>Fan Kit</b>	Not included
<b>Fed Type</b>	Copper fed
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Class</b>	Low
<b>Powering Type</b>	PoE powered

## Electrical Specifications

<b>License Band</b>	AWS 1700   CEL 850   PCS 1900   SMR 800   USA 700   USA 750
<b>Voltage Range</b>	-60 to -36 Vdc

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

