


552466-2



PICABOND® Connector, 250 loose piece, 48 Vdc, pink

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

OBSOLETE

This product was discontinued on: June 1, 2016

Replaced By:

552466-4	PICABOND® Connector, 250 loose piece, 400 Vdc, pink
552466-6	PICABOND® Connector LOOSE PIECE, PINK

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Splice
Product Brand	PICABOND®
Product Series	PICABOND

General Specifications

Connector Color Code	Pink
Connector Sealant	Unfilled
Connector Splicing Type	High Count Straight

Dimensions

Compatible Conductor Gauge, solid	28–24 AWG
--	-----------

Electrical Specifications

Safety Voltage Rating	48 Vdc
------------------------------	--------

Material Specifications

Contact Base Material	Brass
Contact Plating Material	Tin

552466-2

Insulation Material

Air Core PIC | Paper or Pulp

Environmental Specifications

Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

Environmental Space

Outdoor

Packaging and Weights

Packaging quantity

250

Packaging Type

Loose piece

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

