

# 1132DZ

---

Splice for elliptical waveguide 132

## Product Classification

**Product Type** Elliptical waveguide connector

## General Specifications

**Attachment Method** Tab-flare | Tool-flare

**Body Style** Splice

**Inner Contact Plating** Unplated

**Interface** Splice

**Outer Contact Plating** Unplated

**Pressurizable** Yes

## Dimensions

**Width** 53.34 mm | 2.1 in

**Length** 68.834 mm | 2.71 in

## Electrical Specifications

**Insertion Loss, typical** 0.01 dB

**Operating Frequency Band** 14.0 – 15.35 GHz

## Material Specifications

**Material Type** Brass

## Environmental Specifications

**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

## Packaging and Weights

**Weight, net** 0.7 kg | 1.543 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# 1132DZ

---



## \* Footnotes

**Insertion Loss, typical**  $0.05\sqrt{\text{freq}}$  (GHz) (not applicable for elliptical waveguide)