

1635C



Fixed-tuned UG-344/U for elliptical waveguide 63

Product Classification

Product Type Elliptical waveguide connector

General Specifications

Attachment Method Tab-flare | Tool-flare

Body Style Straight, fixed-tuned

Inner Contact Plating Unplated

Interface UG-344/U

Outer Contact Plating Unplated

Pressurizable Yes

Dimensions

Width 85.852 mm | 3.38 in

Length 85.344 mm | 3.36 in

Transition Length 52.832 mm | 2.08 in

Waveguide Size WR137 | WG14 | R70

Electrical Specifications

Insertion Loss, typical 0.01 dB

Operating Frequency Band 5.925 – 7.125 GHz

Peak Power at Frequency, maximum 102.00 kW @ 6.78 GHz

Material Specifications

Material Type Brass

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

1635C

Packaging and Weights

Weight, net 1.7 kg | 3.748 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss, typical $0.05\sqrt{\text{freq}}$ (GHz) (not applicable for elliptical waveguide)