

# 5504649-8

---

Fiber Optic FC Kit, singlemode, BP, blue, 3 m

## OBSOLETE

This product was discontinued on: March 1, 2018

## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Regional Availability</b> | Asia   Latin America   North America |
| <b>Portfolio</b>             | NETCONNECT®                          |
| <b>Product Type</b>          | Fiber connector                      |

## General Specifications

|                    |           |
|--------------------|-----------|
| <b>Body Style</b>  | One-piece |
| <b>Boot Style</b>  | Short     |
| <b>Color</b>       | Silver    |
| <b>Color, boot</b> | Blue      |
| <b>Interface</b>   | FC/UPC    |

## Dimensions

|                                  |                 |
|----------------------------------|-----------------|
| <b>Compatible Cable Diameter</b> | 3 mm   0.118 in |
|----------------------------------|-----------------|

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Packaging and Weights

|                           |     |
|---------------------------|-----|
| <b>Packaging quantity</b> | 500 |
| <b>Packaging Type</b>     | Bag |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>                                                                                                           |
|---------------|---------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS    | Above maximum concentration value                                                                                               |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted                                                                                                              |
| UK-ROHS       | Compliant/Exempted                                                                                                              |

5504649-8

---

