



PICABOND® Connector, 1000 strip, mini, brown

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

OBSOLETE

This product was discontinued on: December 30, 2020

Product Classification

| | |
|------------------------------|--|
| Regional Availability | Australia/New Zealand EMEA Latin America North America |
| Product Type | Splice |
| Product Brand | PICABOND® |
| Product Series | PICABOND |

General Specifications

| | |
|--------------------------------|---------------------|
| Connector Color Code | Brown |
| Connector Sealant | Unfilled |
| Connector Splicing Type | High Count Straight |

Dimensions

| | |
|--|-----------|
| Compatible Conductor Gauge, solid | 24–19 AWG |
|--|-----------|

Electrical Specifications

| | |
|------------------------------|---------|
| Safety Voltage Rating | 400 Vdc |
|------------------------------|---------|

Material Specifications

| | |
|---------------------------------|------------------------------|
| Contact Base Material | Phosphor Bronze |
| Contact Plating Material | Tin |
| Insulation Material | Air Core PIC Paper or Pulp |

552043-3

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +60 °C (-40 °F to +140 °F) |
| Environmental Space | Outdoor |

Packaging and Weights

| | |
|---------------------------|-------|
| Packaging quantity | 1000 |
| Packaging Type | Strip |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |

