


EH9470-000 | OC-ADP-L2-L2-NNCD



Fiber Optic Duplex Adapter, Singlemode LC/APC, green, with flanges

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

OBSOLETE

This product was discontinued on: June 1, 2022


Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber adapter
Product Series	OC-ADP

General Specifications

Body Style	Duplex
Color	Green
Interface	LC/APC
Mounting	Square flange
Total Ports, quantity	2
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Outline Drawing



Material Specifications

Alignment Sleeve Material Ceramic

Mechanical Specifications

Coupling Retention Force 70 N | 15.737 lbf

Optical Specifications

Fiber Mode Singlemode

Insertion Loss, maximum 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity 1

Packaging Type Bag