



M4800A 1U Angled Panel, 48 port, for UNIPRISE Category 5e, 6A and 6 Jacks

- Available for use with the DYMO® labeling solution

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	RJ45 patch panel

## General Specifications

<b>ANSI/TIA Category</b>	5e   6   6A
<b>Color</b>	Black
<b>Intelligence Type</b>	Passive
<b>Panel Style</b>	Angled
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	143 mm   5.63 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Steel
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

