

# FD3-AJ864J00PFFP5X



FDH 3000 Large PFP cabinet, 864-Pos, SC/APC, No Splitters, Dry-Dry Single Armor Ribbon OSP, 300ft, 288f. Feeder, (2) 432f. Distribution, 48.74"H\* x 47.39"W x 19.58"D

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front and rear door
<b>Cable Type</b>	Armored - Ribbon
<b>Distribution Cables, quantity</b>	2
<b>Distribution Ports, quantity</b>	864
<b>Fibers per Distribution Cable, quantity</b>	432
<b>Fibers per Feeder Cable, quantity</b>	288
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pad

## Dimensions

<b>Height</b>	1,238.25 mm   48.75 in
<b>Width</b>	1,220.47 mm   48.05 in
<b>Depth</b>	497.33 mm   19.58 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Large

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

# FD3-AJ864J00PFFP5X

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

