

760239237 | Pole Base 4G/5G, Round 12 in dia



Round 12 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Pole top concealment module for LAA/CBRS radio mounting
- Base of 12in diameter accepts up to (4) low power radios
- Concealment integrates AC load center/OVP and disconnect

Product Classification

Product Type Metro cell site enclosure

General Specifications

Color Light Grey (RAL 7035)

Color Notes 760239237AB1HH - Light Grey | 760239237AB2HH - Green | 760239237AB3HH - Black | 760239237AB4HH - Brown | 760239237AB5HH - Beige-Grey | 760239237AB9HH - Metallic Silver | 760239237ABCCHH - Faux Concrete | 760239237ABWHH - Pure White

Color Options Beige-Grey (RAL 7006) | Black | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White

Cooling Passive Cooling

Radio Compatibility, Ericsson (3) 2205/2208 (Pole Top) | (4) 2203 (radio concealment module) | 5G Expansion module included | 760239237E

Radio Compatibility, Nokia (2) Airscale Micro Radios - LAA & CBRS (Pole Top) | (2) Airscale micro radios – (radio concealment module) | 5G Expansion module included | 760239237N

Radios Included None

Dimensions

Height Note 5 ft tall Equipment Base | 5.5 ft tall Radio Concealment Module

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Depth 325.12 mm | 12.8 in

Depth Note Round

Pole Diameter 203.2 mm | 8 in

760239237 | Pole Base 4G/5G, Round 12 in dia

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487

* Footnotes

Pole Height Options Overall AGL Standard Height