FGS-HNTS-5/8-LP



FiberGuide® Low-Profile Top Support C-Bracket Kit, 5/8in for 2x6, 4x4, 4x6in Systems

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Support mounting kit

Product Brand FiberGuide®

Product Series FGS

General Specifications

ColorBlackOrientationHorizontalSection TypeBracket

Dimensions

 Height
 203.2 mm | 8 in

 Width
 38.1 mm | 1.5 in

 Length
 203.2 mm | 8 in


Thread Size 5/8 in

System Dimensions 102 mm x 102 mm (4 in x 4 in) | 102 mm x 152 mm (4 in x 6 in) | 51 mm x 152 mm (2 in x 6 in)

Ordering Tree



FGS-HNTS-5/8-LP



Material Specifications

Material Type Carbon steel

Packaging and Weights

Included Hardware

Packaging quantity

Weight, net 0.866 kg | 1.909 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINIA-DOHS	Below maximum cond

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

