FGS-HTHR-1/2-12



FiberGuide® Threaded rod, 1/2in Diameter, 12in Length

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Threaded rod **Product Type**

Product Brand FiberGuide®

Product Series FGS

General Specifications

Color Silver

Orientation Horizontal **Section Type** Mounting

Dimensions

Length mm | 12 in

Rod Length 304.8 mm | 12 in

Thread Size 1/2 in

Ordering Tree



FGS-HTHR-1/2-12

Rod Diameter

| 9 | 1/2 | 1/2 in |
|---|-------|--------|
| | 5/8 | 5/8 in |
| | 12 MM | 12 mm |
| | 14 MM | 14 mm |
| | 16 MM | 16 mm |

^{*} Rod diameter and length needs to be both metric or imperial sized

Rod Length

| 10 | 12 | 12 in |
|----|-------|--------|
| | 30 | 30 in |
| | 48 | 48 in |
| | 72 | 72 in |
| | 30CM | 30 cm |
| | 75CM | 75 cm |
| | 180CM | 180 cm |

Packaging and Weights

Weight, net 0 kg | 0 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

