

# LSX-T7/OZD061

---



LSX Fiber Term Panel 6 Ru, 144 - SC/UPC, Singlemode IFC Stranded, 61 Meters, Far end connection Stub

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel, with IFC cable
<b>Product Series</b>	LGX

## General Specifications

<b>Functionality</b>	Patching
<b>Application</b>	Used in LSX-style frames only
<b>Cable Exit Location</b>	Upward
<b>Cable Stub Type</b>	IFC, stranded
<b>Color</b>	Putty white
<b>Color, front</b>	White
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	Stub tail
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	6
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	144

## Dimensions

<b>Height</b>	228.6 mm   9 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	304.8 mm   12 in
<b>Cable Length</b>	61 m   200.131 ft

# LSX-T7/OZD061

---

## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

