

FPM-0M/O-M003M

Fiber Optic Pigtail, OS2, LC/APC-stub, 12F soft wall 900 μ m buffered fiber, 3 m, yellow, 12" breakout

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber pigtail, multi-fiber
Product Series	FPM

General Specifications

Connector A, quantity	12
Color, boot A	Green
Color, connector A	Green
Construction Type	Stranded
Interface, Connector A	LC/APC
Jacket Color	Yellow
Total Fibers, quantity	12

Dimensions

Cord Length	3 m 9.843 ft
--------------------	----------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.35 dB
Return Loss, minimum, connector A	65 dB

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

FPM-0M/0-M003M

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

