

TFAM91/21-14



ION®-B Series Medium Power Remote Unit for EGSM 900 and UMTS

OBSOLETE

Product Classification



Product Type	Remote unit
Product Brand	ION®-B

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	Medium

Dimension Drawing

TFAM91/21-14



Electrical Specifications

Impedance	50 ohm
License Band	EGSM 900 UMTS
Voltage Range	85 to 265 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	1920 – 1980 MHz (UMTS) 880 – 915 MHz (EGSM 900)
---------------------------------	---

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	2110 – 2170 MHz (UMTS) 925 – 960 MHz (CEL 900)
---------------------------------	--

Regulatory Compliance/Certifications

TFAM91/21-14

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted



Included Products

TPSN1/05-40 – Power Supply Adapter ION®-B Series Remote Units, 40 W

TPSN1/05-40



Power Supply Adapter ION®-B Series Remote Units, 40 W

Product Classification

Product Type	Power adapters
Product Brand	ION®-B

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
-------------	--

Dimension Drawing

Electrical Specifications

Output Power, maximum	40 W
------------------------------	------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

