

TPO180/92/19E



ION®-B Series Multiband RF Point of Interface for LMR 800, LMR900, and PCS 1900 Extended

OBSOLETE

Product Classification

Product Type Point of interface
Product Brand ION®-B

General Specifications

Note Detailed Product Specifications are available. Please contact your local CommScope representative.

Electrical Specifications

Impedance 50 ohm
License Band LMR 800 | LMR 900 | PCS 1900 Extended

Electrical Specifications, Tx (Downlink)

Operating Frequency Band 1930 – 1995 MHz (PCS 1900 Extended) | 851 – 869 MHz (LMR 800) | 935 – 941 MHz (LMR 900)

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

