

# 760244689 | DM12-24LCA-SM-AF

---

G2 MPOptimate® Singlemode MPO-12 Distribution Module, 24LC APC to 2x12f MPO's pinned, internal shutters

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Series</b>	G2

## General Specifications

<b>Functionality</b>	Breakout
<b>Color, front</b>	Green
<b>Color, rear</b>	Black
<b>Interface, front</b>	LC/APC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Key up/down   Pinned
<b>Polarity</b>	Method A   Pairs, flipped
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Height</b>	26.42 mm   1.04 in
<b>Width</b>	96.52 mm   3.8 in
<b>Depth</b>	117.35 mm   4.62 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum</b>	1.05 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
--------------------------------	---------------------------

# 760244689 | DM12-24LCA-SM-AF

---

**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 0.113 kg | 0.249 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

