

# 760042960 | MIR-RJ45

---

## M-Series Ruggedized Receptacle, RJ45

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Adapter kit

### General Specifications

<b>ANSI/TIA Category</b>	5e   6   6A
<b>Application</b>	Provides sealed copper connectivity
<b>Color</b>	Black
<b>Total Ports, quantity</b>	1

### Dimensions

<b>Height</b>	35.56 mm   1.4 in
<b>Width</b>	35.56 mm   1.4 in
<b>Depth</b>	25.4 mm   1 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	-25 °C to +85 °C (-13 °F to +185 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

### Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.023 kg   0.05 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# 760042960 | MIR-RJ45

---

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

