

IR22SP 2-port Double Gang Stainless Steel Industrial Faceplate

OBSOLETE

This product was discontinued on: December 31, 2018

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Faceplate kit

General Specifications

ANSI/TIA Category	5e 6 6A
Application	Used with M Series modular information outlet
Color	Silver
Mounting	Flush
Total Ports, quantity	2

Dimensions

Height	114.3 mm 4.5 in
Width	115.824 mm 4.56 in
Receptacle Opening	27.94 mm 1.1 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Environmental Specifications

Operating Temperature	-25 °C to +85 °C (-13 °F to +185 °F)
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529: 2001, IP44
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

