### GigaSPEED X10D® XL® M2000 U/UTP Modular Panel 2U Cord Manager Kit

#### OBSOLETE

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America	
Portfolio	CommScope®	
Product Type	Horizontal cable management	
Product Brand	GigaSPEED X10D®	

# General Specifications

ANSI/TIA Category	3   5   5e   6   6A
Configuration Type	Single-sided
Color	Black
Total Ports, quantity	48

#### Dimensions

Height	82.55 mm	3.25 in
Width	9.652 mm	0.38 in
Depth	95.25 mm	3.75 in

#### Material Specifications

Material Type Powder-coated steel

# **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	UL   cUL

## Packaging and Weights

Packaging quantity

# Regulatory Compliance/Certifications

5

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 24, 2023



# 760073486 | M2000 CM kit

#### Agency

#### Classification

ISO 9001:2015



Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 24, 2023

