

OCC1A Wideband Splitter, singlemode, 1x2, 95/5 ratio, 0.250 mm cable, field installable



Product Classification

Regional Availability	North America
Product Type	Splitter component
Product Series	OCC1A

General Specifications

Device Type	Component, tubular
Functionality	Splitting
Technology Type	Fused biconic tapered
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	1 x 2 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	95/5
Splitter, quantity	1

Dimensions

Pigtail length, input	2.5 m 8.202 ft
Pigtail length, output	2.5 m 8.202 ft
Pigtail Diameter	0.25 mm 0.01 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

