# 195714-000 | OCC1A-1205-NNANQNF

OCC1A Wideband Splitter, singlemode, 1x2, 95/5 ratio, 0.250 mm cable, field installable



## Product Classification

Regional Availability	North America
Product Type	Splitter component
Product Series	OCC1A

## General Specifications

Device Type	Component, tubular
Functionality	Splitting
Technology Type	Fused biconic tapered
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	1 x 2 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	95/5
Splitter, quantity	1

### Dimensions

Pigtail Length, Input	2.5 m   8.202 ft
Pigtail Length, Output	2.5 m   8.202 ft
Pigtail Diameter, Input	0.25 mm   0.01 in
Pigtail Diameter, Output	0.25 mm   0.01 in

## Packaging and Weights

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023



# 195714-000 | OCC1A-1205-NNANQNF

#### Packaging quantity

## Regulatory Compliance/Certifications

#### Agency

#### Classification

1

CHINA-ROHS

### REACH-SVHC

ROHS

UK-ROHS

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

