

# 7801340 | SFP+, 10GBase CWDM-490, 40km

---



Small form factor pluggable+ Module, 10G BASE, CWDM, Singlemode

## Product Classification

**Product Type** Optical module

## General Specifications

**Input Connector Interface** LC

**Note** Detailed Product Specifications are available. Please contact your local CommScope representative.

## Dimensions

**Height** 12 mm | 0.472 in

**Width** 14 mm | 0.551 in

**Depth** 57 mm | 2.244 in

## Optical Specifications

**Fiber Type** 9/125  $\mu\text{m}$ , singlemode

**Wavelength** 1491 nm

## Environmental Specifications

**Operating Temperature** 0 °C to +70 °C (+32 °F to +158 °F)