

# L2-PSMSM-20M-HF

---

LDF2-50 Jumper with interface types SMA Male and SMA Male, 20M



## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Series</b>	LDF2-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	SMA Male
<b>Interface, Connector B</b>	SMA Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	20 m   65.617 ft
<b>Nominal Size</b>	3/8 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
45–13000 MHz	1.58	13

## Jumper Assembly Sample Label

# L2-PSMSM-20M-HF

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Included Products

- L2TSM-PL - SMA Male Positive Lock for 3/8 in LDF2-50 cable
- LDF2-50 - LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket