

M63215-000 | OCC1D-X-440-NNNQF



OCC1D DWDM, 1 channel, double demux, 1542.14 nm starting wavelength, 0.250 mm cable, light duty housing, field installable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	DWDM component
Product Series	OCC1D

General Specifications

Device Type	Component, rectangular
Functionality	Demultiplexing
Technology Type	Thin film filter (TFF)
Application	For use in FOSC closures
Circuits, quantity	2
Distribution Type	1-channel DWDM
Interface, Input	Stub tail
Interface, Output	Stub tail
Multiplexers, quantity	2

Dimensions

Pigtail length, input	2.5 m 8.202 ft
Pigtail length, output	2.5 m 8.202 ft
Pigtail Diameter	0.25 mm 0.01 in

Optical Specifications

Starting Wavelength	1,542.14 nm
----------------------------	-------------

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

