

# NPP06SZDB

## Base Product



## NPP RJ45 Patch Cord, category 6, Shielded, LSZH, Eco-packaging

- High-performance patch cords exceeding industry standards supporting NETCONNECT channel specifications
- Standardized transparent, slim-line boots provides consistent patch cord appearance and supports highest density applications
- Colored clips are available to fit the transparent boot, eliminating the need of multiple colors for matching every jacket color
- Colored pull latch tabs are available for easier plug release handling from the modular jack

## Product Classification

<b>Regional Availability</b>	Asia   EMEA
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord
<b>Product Series</b>	NPC
<b>Ordering Note</b>	Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	S/FTP (shielded)
<b>Conductor Type</b>	Stranded
<b>Interface, Connector A</b>	RJ45 plug
<b>Interface Feature, connector A</b>	Standard
<b>Interface, Connector B</b>	RJ45 plug
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	Black   Blue   Green   Orange   Pink   Purple   Red   Slate   Violet   White   Yellow
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	IEEE 802.3bt Type 4
<b>Wiring</b>	T568B

## Dimensions

<b>Cable Assembly Length Range (m)</b>	1 – 30
<b>Cable Assembly Length Range (ft)</b>	4 – 100

# NPP06SZDB

<b>Cable Assembly Length Range (cm)</b>	100 – 999
<b>Cable Assembly Length Range (in)</b>	48 – 999
<b>Diameter Over Jacket</b>	5.84 mm   0.23 in
<b>Compatible Conductor Gauge, stranded</b>	26 AWG

## Ordering Tree

NPP       -  <sup>10</sup>  OR  <sup>12</sup>     <sup>11</sup>

### Jacket Color

10	BK	Black
	BL	Blue
	GN	Green
	GY	Gray
	OR	Orange
	PK	Pink
	RD	Red
	VT	Violet
	WT	White
	YL	Yellow

### UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

### Length

12  XXX

### Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Environmental Space** Low Smoke Zero Halogen (LSZH)

**Safety Standard** UL 1863

## Packaging and Weights

**Packaging Material** Eco-friendly, single-use plastics-free

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

# NPP06SZDB

---

RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

2843032-3 MP-Boot-S/SL-AB	-	Modular Plug Shielded Slim-Line Boot for Category 6A/6 and Category 5e EMT Plugs, 4.7 to 6.0 mm, transparent
6-2111989-3 MP-6S-C-1	-	Modular Plug Kit, category 6, shielded, 8-position, 5.7 – 7.0 mm max cable jack OD, 100/bag

# 2843032-3 | MP-Boot-S/SL-AB



Modular Plug Shielded Slim-Line Boot for Category 6A/6 and Category 5e EMT Plugs, 4.7 to 6.0 mm, transparent

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Modular plug boot

## General Specifications

<b>Boot Feature</b>	Color-clip compatible   Pull-tab compatible   Shielded   Slimline   Snagless
<b>Color</b>	Clear
<b>Compatible Plug Type</b>	Cat 5e   Cat 6   Cat 6A

## Dimensions

<b>Compatible Cable Diameter, maximum</b>	6 mm   0.236 in
<b>Compatible Cable Diameter, minimum</b>	4.7 mm   0.185 in


## Packaging and Weights

<b>Included</b>	Strain relief
<b>Packaging quantity</b>	100
<b>Packaging Type</b>	Bag   Box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





Modular Plug Kit, category 6, shielded, 8-position, 5.7 – 7.0 mm max cable jack OD, 100/bag

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Modular plug

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	Round, shielded
<b>Conductor Type</b>	Solid   Stranded
<b>Interface</b>	RJ45
<b>Positions/Loaded Contacts</b>	8/8
<b>Termination Type</b>	IDC

## Dimensions

<b>Compatible Cable Diameter, maximum</b>	7 mm   0.276 in
<b>Compatible Cable Diameter, minimum</b>	5.7 mm   0.224 in
<b>Compatible Insulated Conductor Diameter, maximum</b>	1.09 mm   0.043 in
<b>Compatible Insulated Conductor Diameter, minimum</b>	0.89 mm   0.035 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	26–23 AWG
<b>Compatible Conductor Gauge, stranded</b>	26–23 AWG

## Electrical Specifications

<b>Insulation Resistance, minimum</b>	500 mOhm
---------------------------------------	----------

## Material Specifications

<b>Contact Base Material</b>	Phosphor Bronze
<b>Contact Plating Material</b>	Gold
<b>Material Type</b>	Glass filled polycarbonate
<b>Plug Shield Base Material</b>	Stainless steel
<b>Plug Shield Plating Material</b>	Nickel

## Mechanical Specifications

<b>Plug Insertion Life, minimum</b>	750 times
-------------------------------------	-----------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	UL 1863

## Packaging and Weights

<b>Packaging quantity</b>	100
<b>Packaging Type</b>	Bag   Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

