

MGS Icon Strip, Red (25 ea/pkg)



## OBSOLETE

### Replaced By:

760103812  
M61K-ICON-RD

MGS Icon Strip (Voice / Data / Blank), Red (25 ea/pkg)

## Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio** SYSTIMAX®

**Product Type** Icon kit

## General Specifications

**Color** Red

## Material Specifications

**Material Type** High-impact, flame retardant, thermoplastic

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging quantity** 25

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

