



## M14SP 4-port Single Gang Stainless Steel Faceplate

### Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Faceplate kit   |
| <b>Product Series</b>        | M Series  |

### General Specifications

|                              |   |
|------------------------------|---|
| <b>Application</b>           | Used with M Series modular information outlet |
| <b>Mounting</b>              | Flush   |
| <b>Total Ports, quantity</b> | 4   |

### Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 114.3 mm   4.5 in  |
| <b>Width</b>  | 69.85 mm   2.75 in |
| <b>Depth</b>  | 4.064 mm   0.16 in |

### Material Specifications

|                      |                 |
|----------------------|-----------------|
| <b>Material Type</b> | Stainless steel |
|----------------------|-----------------|

### Environmental Specifications

|                        |          |
|------------------------|----------|
| <b>Safety Standard</b> | UL   cUL |
|------------------------|----------|

### Packaging and Weights

|                           |                    |
|---------------------------|--------------------|
| <b>Packaging quantity</b> | 1                  |
| <b>Weight, net</b>        | 0.068 kg   0.15 lb |

### Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b> |
|---------------|-----------------------|
|---------------|-----------------------|

# 108615204 | M14SP

---

|               |  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

