F1-XMHM-3-SGW1-D



D-CLASS FSJ1-50A SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male, with HELIAX® SureGuard weatherproofing boot on HM end only, 3 ft

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product TypeWireless transmission cable assembly

Product Series FSJ1-50A

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A Nex10 Male

Interface, Connector B 4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 0.914 m | 2.999 ft

Nominal Size 1/4 in

Electrical Specifications

3rd Order IMD Dynamic -119 dBm

3rd Order IMD Dynamic Test MethodTwo +43 dBm carriers per IEC 62037

Logo Image



F1-XMHM-3-SGW1-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.07	30
1700-2200 MHz	1.09	28
2500-2700 MHz	1.11	26
3400-3800 MHz	1.23	20

Jumper Assembly Sample Label



COMMSC**O**PE°

F1-XMHM-3-SGW1-D

Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

