

FGS-DSHC-A



FiberGuide® Split Hinged Cover Kit for Straight Section, 4x4in, Yellow

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber raceway cover |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|---------------------|------------------|
| Color | Yellow |
| Orientation | Horizontal |
| Section Type | Straight Section |

Dimensions

| | |
|--------------------------|-------------------------------|
| Height | 101.6 mm 4 in |
| Width | 101.6 mm 4 in |
| System Dimensions | 102 mm x 102 mm (4 in x 4 in) |

Material Specifications

| | |
|----------------------|---------------------------|
| Material Type | Engineering Thermoplastic |
|----------------------|---------------------------|

Environmental Specifications

| | |
|--------------------------------|--------------------------------|
| Flammability Rating | CSA S143 UL 2024 UL 94 V-0 |
| Halogen Characteristics | Blue Angel TCO '99 WEEE |
| Safety Standard | CSA UL |

Packaging and Weights

| | |
|--------------------|---------------------|
| Weight, net | 1.519 kg 3.349 lb |
|--------------------|---------------------|

FGS-DSHC-A

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

