


# FGS-HNTR-F-12MM

---



FiberGuide® New Threaded Rod Bracket Kit, 12mm for 4x12in System

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS
<b>Minimum Order Quantity</b>	12

## General Specifications

<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket
<b>Bracket Type</b>	Cantilever
<b>Bracket Installation Type</b>	New
<b>Attachment Type</b>	Threaded rod

## Dimensions

<b>Height</b>	31.75 mm   1.25 in
<b>Width</b>	50.8 mm   2 in
<b>Length</b>	419.1 mm   16.5 in
<b>Thread Size</b>	12 mm
<b>System Dimensions</b>	102 mm x 305 mm (4 in x 12 in)

## Ordering Tree

# FGS-HNTR-F-12MM

FGS - HNTR - <sup>9</sup>F - <sup>10</sup>5/8

## For Section Size

9	empty	4 x 4 in, 4 x 6 in
	F	4 x 12 in

## For Threaded Rod Size

10	1/2	1/2 in
	12MM	12 mm
	14MM	14 mm
	16MM	16 mm
	3/8	3/8 in
	5/8	5/8 in
	5/8-A	5/8 in, modified
	5/8-S	5/8 in, short
	5/8-XA	5/8 in, x-aisle

## Material Specifications

**Material Type** Steel

## Packaging and Weights

**Included** Hardware

**Packaging quantity** 1

**Weight, net** 1.12 kg | 2.469 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](https://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

