

# FGS-KIT-H44

---



FiberGuide® Vertical Straight Section with 2in Slot Spacing, Trumpet Flares and Cover, 4x4in, Yellow

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Slotted vertical with snap-on cover
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Product Feature</b>	Slotted
<b>Color</b>	Yellow
<b>Orientation</b>	Vertical
<b>Section Type</b>	Straight section

## Dimensions

<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)
--------------------------	-------------------------------

## Material Specifications

<b>Material Type</b>	Engineering Thermoplastic
----------------------	---------------------------

## Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

## Packaging and Weights

<b>Weight, net</b>	3.207 kg   7.07 lb
--------------------	--------------------

## Regulatory Compliance/Certifications

# FGS-KIT-H44

---

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

