FGS-MHRT-F-VS



FiberGuide® Variable Support Kit for 4x12in Tee Section

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Support mounting kit

Product Brand FiberGuide®

Product Series FGS

General Specifications

Product Feature Transition

Color Black

OrientationHorizontalSection TypeTee section


Dimensions

System Dimensions 102 mm x 305 mm (4 in x 12 in)

Ordering Tree



FGS-MHRT-F-VS



Section Size 4 x 4 in 10 4 x 6 in 4 x 6 in, variable support bracket 4 x 12 in 4 x 12 in, 6 in exit 4 x 12 in, 6 in exit, with variable support bracket 4 x 12 in, 6 in exit, variable support bracket F/B-VS 4 x 12 in, variable support bracket 2 x 6 in 4 x 24 in 4 x 24 in, 12 in exit 4 x 24 in, 12 in exit, variable support bracket 4 x 18 in 4 x 18 in, 12 in exit 4 x 18 in. 24 in exit 4 x 18 in

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 1.389 kg | 3.062 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



^{*} Support brackets only come in black

FGS-MHRT-F-VS

