FGS-MSHS-CA



FiberGuide® Vertical Straight Section with 1.5in Slot Spacing, Square Opening, 2x2in, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeSlotted verticalProduct BrandFiberGuide®

Product Series FGS

General Specifications

Product Feature Slotted

Color Yellow

Orientation Vertical

Section Type Straight Section

Dimensions

 Height
 50.8 mm | 2 in

 Width
 50.8 mm | 2 in

Length 1829 mm | 72.008 in

System Dimensions 51 mm x 51 mm (2 in x 2 in)

Ordering Tree



FGS-MSHS-CA



Section Color

9	empty	yellow
	В	black

Section Length

11	empty	6 ft
	10	10 ft
	12	12 ft

Section Size

10	А	4 x 4 in
	В	4 x 6 in
	С	2 x 2 in
	D	4 x 4 in, slotted duct, 2 in slot spacing
	F	4 x 12 in
	F-CF	4 x 12 in, with center divider
	G	2 x 6 in
	Н	4 x 24 in
	К	2 x 4 in, slotted duct, 2 in slot spacing
	STOR-B	4 x 6 in, with slack storage spools
	STOR-G	2 x 6 in, with slack storage spools
	STOR-F	4 x 12 in, with slack storage spools

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.408 kg | 0.899 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



COMMSCOPE®

FGS-MSHS-CA

