

D80891-000 | OCC1A-1210-NNASENB



OCC1A Wideband Splitter, singlemode, 1x2, 90/10 ratio, 0.9 mm cable, medium duty housing

OBSOLETE

This product was discontinued on: March 7, 2019

Product Classification

Regional Availability	North America
Product Type	Splitter component
Product Series	OCC1A

General Specifications

Device Type	Component, tubular
Functionality	Splitting
Technology Type	Fused biconic tapered
Application	For use in FOSC closures
Circuits, quantity	1
Distribution Type	1 x 2 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	90/10
Splitter, quantity	1

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter, Input	0.9 mm 0.035 in
Pigtail Diameter, Output	0.9 mm 0.035 in

Packaging and Weights

Packaging quantity 1