

E91273-000 | OCC1P-21600-NNNQNQA



OCC1P Wideband Splitter, planar, singlemode, 2x16, symmetrical split ratio, 0,250 mm cable, light duty housing

OBSOLETE

This product was discontinued on: July 25, 2023

Replaced By:

SP-21600NNNNXABB Wideband PLC Splitter, singlemode, 2x16, symmetrical split ratio, 0.250 mm cable, no connectors
PLC 2X16 250UM NO CONN

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Splitter component
Product Series	OCC1P

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use in FOOSC closures
Circuits, quantity	1
Distribution Type	2 x 16 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter, Input	0.25 mm 0.01 in
Pigtail Diameter, Output	0.25 mm 0.01 in

Environmental Specifications

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

