# 19256B



Lace-up Hoisting Grip for 7/8 in coaxial cable, elliptical waveguide 77, and HELIAX® Hybrid cable

#### **Product Classification**

**Product Type** Hoisting grip

Ordering Note CommScope® standard product (Global)

#### General Specifications

Attachment Spacing Intervals 60.96 m | 200 ft

Hoisting Grip Type Lace-up hoisting grip

Support ClampNot includedTool TypeHoisting grip

#### **Dimensions**

Grip Length, minimum431.8 mm | 17 inLeader Length, minimum330.2 mm | 13 in

Nominal Size 7/8 in

### **Electrical Specifications**

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

# Material Specifications

Material Type Stainless steel

### Mechanical Specifications

Pull Load Capacity 226.796 kg | 500 lb

## Packaging and Weights

 Height, packed
 38.1 mm | 1.5 in

 Width, packed
 218.44 mm | 8.6 in

**COMMSCOPE®** 

# 19256B

**Length, packed** 220.98 mm | 8.7 in

Packaging quantity

**Weight, gross** 0.22 kg | 0.485 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



