

# 209800-28B

---



Self-locking Hanger for 7/8 in RXL5 RADIAX® Radiating cable

**OBSOLETE**

## Product Classification

**Product Type** Hanger kit

## General Specifications

**Cables per Hanger** 1  
**Color** Black  
**Hanger Type** Self locking hanger

## Dimensions

**Maximum Stack Height** 2  
**Height** 49 mm | 1.929 in  
**Width** 20.3 mm | 0.799 in  
**Length** 33.5 mm | 1.319 in  
**Compatible Diameter, maximum** 31.2 mm | 1.228 in  
**Compatible Diameter, minimum** 27.8 mm | 1.094 in  
**Nominal Size** 7/8 in

## Material Specifications

**Material Type** Polyamide PA12

## Mechanical Specifications

**Maximum Load** 850 N | 191.088 lbf

## Environmental Specifications

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

# 209800-28B

---

<b>Flammability Test Method</b>	UL 94-HB
<b>Toxicity Index Test Method</b>	IEC 60754-2
<b>UV Resistance, minimum with no degradation</b>	≥500 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Height, packed</b>	19 cm   7.48 in
<b>Width, packed</b>	11 cm   4.331 in
<b>Length, packed</b>	16.5 cm   6.496 in
<b>Packaging quantity</b>	50
<b>Weight, gross</b>	0.88 kg   1.94 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power