

243095-5



Stainless Steel Hardware Kit for 1/2 in or 7/8 in Double Click-on Hangers, includes 3/8 in bolts and hardware, 137.16 mm (5.4 in) length

Product Classification

Product Type	Hardware kit
Ordering Note	CommScope® standard product (Global)

General Specifications

Thread Size	3/8 in
--------------------	--------

Dimensions

Maximum Stack Height	2
Length	137.16 mm 5.4 in
Nominal Size	1/2 in 7/8 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Packaging and Weights

Height, packed	149.86 mm 5.9 in
Width, packed	63.5 mm 2.5 in
Length, packed	63.5 mm 2.5 in
Included	Forty flat washers Forty lock washers Ten 3/8 in threaded rods Twenty hex nuts
Packaging quantity	10
Weight, gross	1.129 kg 2.49 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



243095-5

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power