



Single Entrance Panel for elliptical waveguide 63

Product Classification

Product Type Entrance panel

General Specifications

Color Gray
Entry Panel Port Size 101.6 mm | 4 in
Number of Ports 1
Panel Type Single

Dimensions

Height 76.2 mm | 3 in
Width 127 mm | 5 in
Waveguide Size WR137 | WG14 | R70

Material Specifications

Material Type Aluminum

Environmental Specifications

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529.14.2

Packaging and Weights

Height, packed 180.34 mm | 7.1 in
Width, packed 180.34 mm | 7.1 in
Length, packed 180.34 mm | 7.1 in
Included Boot | Plate

245314-63

Packaging quantity 1
Weight, gross 0.91 kg | 2.006 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant



Included Products

- 204673-1 - 1 Port Entrance Panel 1 x 1
- WGB4-63 - Boot Assembly, 4 in, for elliptical waveguide 63