

42396A-5



Butterfly Hanger for 7/8 in coaxial cable and elliptical waveguide 85 and 90

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Standard butterfly hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	0
Height	41.9 mm 1.65 in
Width	38.1 mm 1.5 in
Length	63.5 mm 2.5 in
Compatible Cable Diameter Range	26.7–31 mm
Compatible Diameter, maximum	31 mm 1.22 in
Compatible Diameter, minimum	26.7 mm 1.051 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

42396A-5

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

Packaging and Weights

Height, packed

25.4 cm | 10 in

Width, packed

9.5 cm | 3.74 in

Length, packed

11.4 cm | 4.488 in

Packaging quantity

10

Weight, gross

0.49 kg | 1.08 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power