

BC-30-10D



Pipe-to-Pipe Clamp, joins two 1-1/2 in to 3-1/2 in OD round members

Product Classification

Product Type Clamp set

General Specifications

Mounting Pipe-to-pipe

Taper Non-tapered | Tapered

Dimensions

Height 127 mm | 5 in

Width 203.2 mm | 8 in

Length 254 mm | 10 in

Mounting Diameter 2, maximum 88.9 mm | 3.5 in

Mounting Diameter 2, minimum 38.1 mm | 1.5 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 12.2 kg | 26.896 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ROHS

Classification

Above maximum concentration value

Compliant/Exempted

BC-30-10D

UK-ROHS

Compliant/Exempted

