

# CC-215-6

---



Crossover Clamp, joins 2-1/2 in to 3-1/2 in OD pipe to 2-3/8 in to 5 in OD pipe

## Product Classification

**Product Type** Clamp set

## General Specifications

**Mounting** Crossover clamp

**Taper** Non-tapered

## Dimensions

**Height** 127 mm | 5 in

**Width** 203.2 mm | 8 in

**Length** 127 mm | 5 in

**Mounting Diameter 2, maximum** 127 mm | 5 in

**Mounting Diameter 2, minimum** 60.96 mm | 2.4 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 63.5 mm | 2.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamp halves | Threaded rod

**Packaging quantity** 1

**Weight, net** 4.1 kg | 9.039 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

# CC-215-6

---

