

CH-1-58-85M-KT-25

Metal Hanger Kit for 1-5/8 in RADIAX® Radiating cable, Standoff included



Product Classification

Product Type	Hanger kit
Product Brand	RADIAX®

General Specifications

Accessories	Hangers
Cable Type	Smoothwall
Cables per Hanger	1
Color	Silver
Hanger Type	Hanger kits

Dimensions

Maximum Stack Height	1
Nominal Size	1-5/8 in
Hanger Spacing, maximum	10 m 32.808 ft

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Environmental Specifications

Operating Temperature	-30 °C to +80 °C (-22 °F to +176 °F)
------------------------------	--------------------------------------

Packaging and Weights

Height, packed	30 cm 11.811 in
Width, packed	24 cm 9.449 in

CH-1-58-85M-KT-25

Length, packed	27 cm 10.63 in
Packaging quantity	25
Weight, gross	4.2 kg 9.259 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power