

CM-R78



Round Chimney Mount, 7-8 ft OD

Allows for standard sector frame to be mounted to a chimney utilizing (2) "760258156-001" interface brackets per sector frame. Ordered separate.

Sector frames ordered separate.

Site engineer of record to determine capacity and structure suitability for installation.

Product Classification

Product Type	Chimney mount
Ordering Note	ANDREW® non-standard product
Warranty	One year

General Specifications

Mounting	Round Chimneys, 2.13-2.44 m (7-8 ft) OD
-----------------	---

Dimensions

Height	609.6 mm 24 in
Width	1524 mm 60 in
Length	1524 mm 60 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

CM-R78

Included Brackets | Hardware

Packaging quantity 1

Weight, net 136.1 kg | 300.049 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code