

# CV5895-000 | TENIO-C6-TRAY-S24



TENIO™ Splice Tray for large closures (C6 size) for up to 24 heat shrink splice protectors (SMOUV 45 mm)

- Fiber and cable technology independent
- Compatible with G652.D optical fiber

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America
<b>Product Type</b>	Fiber splice tray
<b>Product Series</b>	TENIO

## General Specifications

<b>Color</b>	Gray
<b>Splice Tray Chip Type</b>	Heat shrink
<b>Splice Tray Included, quantity</b>	1
<b>Splices per Tray, quantity</b>	24

## Dimensions

<b>Height</b>	6 mm   0.236 in
<b>Splice Protector Length, maximum</b>	47 mm   1.85 in
<b>Splice Protector Length, minimum</b>	44 mm   1.732 in
<b>Splice Protector Diameter, maximum</b>	2.6 mm   0.102 in
<b>Splice Protector Diameter, minimum</b>	2.2 mm   0.087 in

## Material Specifications

<b>Material Type</b>	PBT   PET
----------------------	-----------

## Mechanical Specifications

<b>Minimum Bend Radius, standard</b>	30 mm   1.181 in
--------------------------------------	------------------

## Environmental Specifications

# CV5895-000 | TENIO-C6-TRAY-S24

---

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Environmental Space** Outdoor

## Packaging and Weights

**Packaging quantity** 8

**Packaging Type** Bag | Carton

**Weight, net** 0.1 kg | 0.22 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

