

CV5897-000 | TENIO-C6-TRAY-A24



TENIO™ Splice Tray for large closures (C6 size) for up to 24 ANT splice protectors

- Fiber and cable technology independent
- Compatible with G652.D optical fiber

Product Classification

Regional Availability	EMEA Latin America
Product Type	Fiber splice tray
Product Series	TENIO

General Specifications

Color	Gray
Splice Tray Chip Type	ANT
Splice Tray Included, quantity	1
Splices per Tray, quantity	24

Dimensions

Height	6 mm 0.236 in
Splice Protector Length, maximum	47 mm 1.85 in
Splice Protector Length, minimum	44 mm 1.732 in
Splice Protector Diameter, maximum	2.6 mm 0.102 in
Splice Protector Diameter, minimum	2.2 mm 0.087 in

Material Specifications

Material Type	PBT PET
----------------------	-----------

Mechanical Specifications

Minimum Bend Radius, standard	30 mm 1.181 in
--------------------------------------	------------------

Environmental Specifications

CV5897-000 | TENIO-C6-TRAY-A24

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Outdoor

Packaging and Weights

Packaging quantity 8

Packaging Type Bag | Carton

Weight, net 0.1 kg | 0.22 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

