

EHO460-000 | TENIO-C6H-TRAY-SLE



TENIO™ Splice Tray for large closures (CH6 size) for up to 24 heat shrink splice protectors (SMOUV 45 mm)

- Fiber and cable technology independent
- Compatible with G652.D optical fiber

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America
Product Type	Fiber splice tray
Product Series	TENIO

General Specifications

Color	Gray
Splice Tray Chip Type	Heat shrink
Splice Tray Included, quantity	1
Splices per Tray, quantity	24

Dimensions

Height	4 mm 0.157 in
Splice Protector Length, maximum	47 mm 1.85 in
Splice Protector Length, minimum	44 mm 1.732 in
Splice Protector Diameter, maximum	2.6 mm 0.102 in
Splice Protector Diameter, minimum	2.2 mm 0.087 in

Material Specifications

Material Type	PBT PET
----------------------	-----------

Mechanical Specifications

Minimum Bend Radius, standard	30 mm 1.181 in
--------------------------------------	------------------

Environmental Specifications

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Outdoor

EHO460-000 | TENIO-C6H-TRAY-SLE

Packaging and Weights

Packaging quantity	12
Packaging Type	Bag Carton
Weight, net	0.1 kg 0.22 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

