

EWSH-64



Universal Snap-in Hanger for elliptical waveguide 64

OBSOLETE

This product was discontinued on: January 2, 2024

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide
Cables per Hanger 1
Color Silver
Hanger Type Snap-in hanger
Mounting 3/4 in through hole

Dimensions

Height 40.9 mm | 1.61 in
Width 59.9 mm | 2.358 in
Length 89.9 mm | 3.539 in
Compatible Diameter, maximum 31 mm | 1.22 in
Compatible Diameter, minimum 26.7 mm | 1.051 in
Waveguide Size WR137 | WG14 | R70

Electrical Specifications

Return Loss Effect, maximum 0.1 dB
DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Stainless steel

EWSH-64

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

Packaging and Weights

Height, packed

20 cm | 7.874 in

Width, packed

20 cm | 7.874 in

Length, packed

20 cm | 7.874 in

Packaging quantity

10

Weight, gross

1.6 kg | 3.527 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

